




Flexible coupling for encoders

COUPLING 25-6-10-24-SV



- 1 M4 x 6 - ISO 4029 (4x)
- 2 Depth der Klemmnabe

Mechanical data		
Weight	[g]	27
Dimensions	[mm]	Ø 25 / L = 24
Materials		aluminium
Tightening torque	[Nm]	tightening torque screws: 120 Ncm
External diameter D	[mm]	25
Inside diameter 1	[mm]	6
Inside diameter 2	[mm]	10
Depth of the clamping hub	[mm]	7
Clamping screw	[mm]	M4 x 6 - ISO 4029 (4x)
Length	[mm]	24
Max. revolution, mechanical	[U/min]	8000
Max. axial shaft misalignment	[mm]	± 0,5
Max. radial shaft misalignment	[mm]	± 0,3
Max. angular displacement	[°]	± 4,0
Remarks		
Remarks	The data indicated apply to couplings with the above hub borings at an ambient temperature of 23 °C.	
	The values of radial, angular and axial displacement are maximum values which must not reach their maximum simultaneously while in operation.	
Pack quantity	1 pcs.	