




Flexible coupling for encoders

COUPLING 19,2-6-6-22-SV



- | | |
|---|------------------------|
| 1 | M3 x 4 - ISO 4029 (4x) |
| 2 | Depth der Klemmnabe |

Mechanical data

Weight	[g]	32.2
Dimensions	[mm]	Ø 19 / L = 22
Materials		aluminium
Tightening torque	[Nm]	tightening torque screws: 80 Ncm
External diameter D	[mm]	19
Inside diameter 1	[mm]	6
Inside diameter 2	[mm]	6
Depth of the clamping hub	[mm]	6
Clamping screw	[mm]	M3 x 4 - ISO 4029 (4x)
Length	[mm]	22
Max. revolution, mechanical	[U/min]	8000
Max. axial shaft misalignment	[mm]	± 0,4
Max. radial shaft misalignment	[mm]	± 0,25
Max. angular displacement	[°]	± 3,5

Remarks

Remarks	The data indicated apply to couplings with the above hub borings at an ambient temperature of 23 °C.
	The values of radial, angular and axial displacement are maximum values which must not reach their maximum simultaneously while in operation.
Pack quantity	1 pcs.