


Connection cable

VDOAH040MSS0001A04STAH040MSS

Article no longer available - archive entry



Electrical data

Operating voltage	[V]	10...30 DC
-------------------	-----	------------

Operating conditions

Ambient temperature	[°C]	-25...90
---------------------	------	----------

Protection	IP 67
------------	-------

Mechanical data

Materials	TPU
Moulded-body material	TPU
Material nut	brass, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



E70054




Connection cable

VDOAH040MSS0001A04STAH040MSS

Electrical connection

Cable: 1 m, PUR / PVC, orange, Ø 5 mm; 4 x 0.25 mm²

Connection



Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

