


E70350



Jumper cable with valve plug

VSTGH050MSS0002B03VDAA041--S



Application		
Special feature	Free from silicone; Halogen-free; Gold-plated contacts	
Free from silicone	yes	
Electrical data		
Operating voltage	[V]	< 24 AC/DC
Overvoltage protection	free-wheeling diode	
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection	IP 67	
Mechanical data		
Weight	[g]	138.8
Materials	TPU	
Moulded-body material	TPU	
Material nut	brass, nickel-plated	
Displays / operating elements		
Display	operation	1 x LED, green
Аксессуары		
Items supplied	screw	
	panel for labelling	

E70350



Jumper cable with valve plug

VSTGH050MSS0002B03VDAA041--S


Remarks

Pack quantity

1 pcs.

Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Contacts: gold-plated



Electrical connection

Cable: 2 m, PUR / PVC, Halogen-free; 3 x 0.5 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x valve type A DIN, angled; Moulded body: TPU; Locking: brass, nickel-plated; Contacts: nickel-plated brass

