




AS-Interface flat cable insulation displacement
connector

FCE Splitter ye/bk ProcessL



Application		
Design	AS-i / 24 V	
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; (AS-i)
Protection class		III
Operating voltage AUX DC	[V]	18...32
Max. current load total	[A]	4; (AS-i: 2 A; AUX: 2 A)
Operating conditions		
Ambient temperature	[°C]	-30...80
Max. relative air humidity	[%]	80; (31 °C; linearly decreasing to 50 % (40 °C))
Max. height above sea level	[m]	2000
Protection		IP 67; IP 68; IP 69K
Pollution degree		2
Tests / approvals		
EMC	EN 61000-6-2	
Mechanical data		
Weight	[g]	112.3
Materials		metal parts: stainless steel (1.4404 / 316L); rubber gasket for contact pins: FPM; O-ring: EPDM
Tightening torque	[Nm]	2.5; (lock nuts)
Аксессуары		
Accessories (optional)	Torque wrench, E70390	
Remarks		
Pack quantity	1 pcs.	




AS-Interface flat cable insulation displacement
connector

FCE Splitter ye/bk ProcessL

Electrical connection - socket

Connector: 1 x M12; coding: A; Tightening torque: 1.2...1.4 Nm



Connection	
1	AS-i +
2	0 V
3	AS-i -
4	+ 24 V
5	n. c.