



Article no longer available - archive entry

Alternative articles: DX2001

When selecting an alternative article and accessories please note that technical data may differ!

# No scale drawing available



Application	
Application	universal evaluation and display for all physical units which can be derived from pulse sequences
Electrical data	
Frequency AC [Hz]	47...63
Operating voltage [V]	230 / 115 AC / 24 DC
Current consumption [mA]	200
Operating conditions	
Ambient temperature [°C]	0...45
Protection	IP 44; (on the front)
Mechanical data	
Type of mounting	panel cutout: 91 x 43 mm
Displays / operating elements	
Display	7-segment LED display, red 6-digit 15 mm
Electrical connection	
Connection	