



Article no longer available - archive entry

No scale drawing available



Application

Application	displaying and monitoring analogue signals; e.g. pressure sensors, temperature sensors or flow sensors
-------------	---

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	200

Operating conditions

Ambient temperature	[°C]	0...45
Protection		IP 44; (on the front)

Mechanical data

Type of mounting	panel cutout: 91 x 43 mm
------------------	--------------------------

Displays / operating elements

Display	7-segment LED display, red 6-digit 15 mm 4 x LED, red
---------	--

Electrical connection

Connection