




Splitter box

ZDO4F049MSJ0005H10



Application

Special feature	Gold-plated contacts; Drag chain suitability
-----------------	--

Electrical data

Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Protection class		III
Max. current load per module/slot	[A]	2
Max. current load total	[A]	6

Outputs

Electrical design	NPN
-------------------	-----

Operating conditions

Ambient temperature	[°C]	-20...80
Ambient temperature (moving)	[°C]	-5...60
Protection		IP 65; IP 67; IP 68

Mechanical data

Weight	[g]	470.5
Dimensions	[mm]	20 x 30 x 85.5



Splitter box

ZDO4F049MSJ0005H10

Materials	PBT-GF20; brass nickel-plated	
Moulded-body material	PBT-GF 20 / brass, nickel-plated	
Number of ports splitter box	4	
Connector type	M8	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ²
	bending cycles	> 5 Mio.
	torsional strain	± 180 °/m

Displays / operating elements

Display	switching status	8 x LED, yellow
	operation	1 x LED, green

Аксессуары

Accessories (optional)	DIN rail adapter:, E73006	
	Protective cap: M8, E73005	

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 5 m, PUR, black, Ø 7.4 mm; 8 x 0.34 mm² (43 x Ø 0.1 mm) + 2 x 0.75 mm² (21 x Ø 0.2 mm)

Electrical connection - slot

Connector: 4 x M8; coding: A; Moulded body: PBT-GF 20 / brass, nickel-plated; Contacts: gold-plated






Splitter box

ZDO4F049MSJ0005H10

Connection



BN =	Core colours :
BU =	brown
GN =	blue
GY =	green
PK =	grey
RD =	pink
WH =	red
YE =	white
	yellow