


## Connection cable

VDOGF030MSS0020H03STGH030MSS

Please see the technical note under "Downloads"



### Application

|                    |  |
|--------------------|--|
| Special feature    | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability |
| Free from silicone | yes  |

### Electrical data

|                         |     |                   |
|-------------------------|-----|-------------------|
| Operating voltage       | [V] | < 50 AC / < 60 DC |
| Protection class        |     | III               |
| Max. current load total | [A] | 3                 |

### Operating conditions

|                                      |      |                             |
|--------------------------------------|------|-----------------------------|
| Ambient temperature                  | [°C] | -25...90                    |
| Note on ambient temperature          |      | cULus: ...75 °C             |
| Ambient temperature (moving)         | [°C] | -25...90                    |
| Note on ambient temperature (moving) |      | cULus: ...75 °C             |
| Protection                           |      | IP 65; IP 67; IP 68; IP 69K |

### Mechanical data

|                        |     |                                   |
|------------------------|-----|-----------------------------------|
| Weight                 | [g] | 596                               |
| Materials              |     | housing: TPU orange; Sealing: FKM |
| Material nut           |     | brass, nickel-plated              |
| Drag chain suitability |     | yes                               |



## Connection cable

VDOGF030MSS0020H03STGH030MSS

|                        |                                 |  |
|------------------------|---------------------------------|--|
| Drag chain suitability | bending radius for flexible use | min. 10 x cable diameter   |
|                        | travel speed                    | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup> |
|                        | bending cycles                  | > 5 Mio.   |
|                        | torsional strain                | ± 180 °/m  |

### Remarks

Notes

Please see the technical note under "Downloads"

Pack quantity

1 pcs.

### Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



### Electrical connection

Cable: 20 m, PUR, Halogen-free, black, Ø 4.3 mm; 3 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Connection



### Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.3...0.5 Nm

