




Inductive AS-Interface sensor

IFK2007-ASI /M/US-104



Product characteristics

Electrical design	AS-i
Sensing range [mm]	7
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 60

Application

Special feature	Gold-plated contacts
Application	Use in machine tools, coolants and lubricants

Electrical data

Operating voltage [V]	26.5...31.6 DC
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	1000

Outputs

Electrical design	AS-i
Switching frequency DC [Hz]	100

Detection zone

Sensing range [mm]	7
Real sensing range S_r [mm]	$7 \pm 10 \%$
Operating distance [mm]	0...5.7

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.5 / copper: 0.4
Hysteresis [X01]	1...20
Switch point drift [X01]	-10...10

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 68; ("Coolant")



Inductive AS-Interface sensor

IFK2007-ASI /M/US-104

Tests / approvals					
EMC	EN 61000-4-2 ESD		4 kV CD / 8 kV AD		
	EN 61000-4-3 HF radiated		10 V/m		
	EN 61000-4-4 Burst		2 kV		
	EN 61000-4-6 HF conducted		10 V		
	EN 55011		class B		
MTTF	[ANN]	1696			
UL approval	Ta		-25...70 °C		
	Enclosure type		Type 1		
	подача напруги		Limited Voltage/Current		
	File number UL		E174191		
AS-i classification					
AS-i version	2.1				
Розширений режим адресації	yes				
AS-i I/O configuration	[hex]	0			
AS-i ID code	[hex]	A.F			
AS-i certificate	57101				
Assignment of the data bits	Designation	switching signal	not used	not used	not used
	status = 0	target outside the active zone	-	-	-
	status = 1	target within the active zone	default value	default value	default value
Mechanical data					
Weight	[g]	32.8			
Housing	threaded type				
Mounting	non-flush mountable				
Dimensions	[mm]	M12 x 1 / L = 60			
Thread designation	M12 x 1				
Materials	stainless steel (1.4404 / 316L); sensing face: LCP uncoloured				
Displays / operating elements					
Display	switching status		4 x 90° LED, yellow		
	function		1 x LED, red		
Аксессуары					
Items supplied	lock nuts: 2				
Remarks					
Pack quantity	1 pcs.				
Electrical connection - plug					
Connector: 1 x M12; coding: A; Contacts: gold-plated					
					

IFC248



Inductive AS-Interface sensor

IFK2007-ASI /M/US-104

Connection

