




Inductive sensor

II-3015-BPKG

Article no longer available - archive entry

Alternative articles: II5300  
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

|                    |                    |
|--------------------|--------------------|
| Electrical design  | PNP                |
| Output function    | normally open      |
| Sensing range [mm] | 15                 |
| Housing            | threaded type      |
| Dimensions [mm]    | M30 x 1.5 / L = 81 |

Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...36 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | yes        |

Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | PNP           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 2.5           |
| Permanent current rating of switching output DC [mA] | 250           |
| Switching frequency DC [Hz]                          | 250           |
| Short-circuit protection                             | yes           |
| Type of short-circuit protection                     | pulsed        |
| Overload protection                                  | yes           |

Detection zone


|                            |           |
|----------------------------|-----------|
| Sensing range [mm]         | 15        |
| Real sensing range Sr [mm] | 15 ± 10 % |
| Operating distance [mm]    | 0...12.1  |



## Inductive sensor

II-3015-BPKG

| Accuracy / deviations         |                                                                             |                    |
|-------------------------------|-----------------------------------------------------------------------------|--------------------|
| Correction factor             | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |                    |
| Hysteresis                    | [X01]                                                                       | 1...15             |
| Switch point drift            | [X01]                                                                       | -10...10           |
| Operating conditions          |                                                                             |                    |
| Ambient temperature           | [°C]                                                                        | -25...80           |
| Protection                    | IP 67                                                                       |                    |
| Tests / approvals             |                                                                             |                    |
| EMC                           | EN 60947-5-2                                                                |                    |
|                               | EN 55011                                                                    | class B            |
| Mechanical data               |                                                                             |                    |
| Housing                       | threaded type                                                               |                    |
| Mounting                      | non-flush mountable                                                         |                    |
| Dimensions                    | [mm]                                                                        | M30 x 1.5 / L = 81 |
| Thread designation            | M30 x 1.5                                                                   |                    |
| Materials                     | PBT                                                                         |                    |
| Displays / operating elements |                                                                             |                    |
| Display                       | switching status                                                            | 1 x LED, yellow    |
| Аксессуары                    |                                                                             |                    |
| Items supplied                | lock nuts: 2                                                                |                    |
| Remarks                       |                                                                             |                    |
| Pack quantity                 | 1 pcs.                                                                      |                    |
| Electrical connection         |                                                                             |                    |
| Cable: 2 m, PVC; 3 x 0.5 mm²  |                                                                             |                    |
| Connection                    |                                                                             |                    |



Core colours :  
 BN = brown  
 BU = blue  
 BK = black