


IS5044

Inductive sensor

IS-2002-FRKG/AS



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	2
Housing	rectangular
Dimensions [mm]	36.8 x 10.2 x 16

Application

Special feature	Increased sensing range
-----------------	-------------------------

Electrical data

Operating voltage [V]	5...36 DC
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Overload protection	yes

IS5044



Inductive sensor

IS-2002-FRKG/AS

Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.62
Increased sensing range		yes
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Impact resistance	EN 60068-2-75 Ehc	
Vibration resistance	EN 60068-2-6 Fc	
Shock resistance	EN 60068-2-27 Ea	
Continuous shock resistance	EN 60068-2-29 Eb	
Fast temperature change	EN 60068-2-14 Na	
Salt spray test	EN 60068-2-52 Kb	
MTTF	[ANN]	2571
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	File number UL	E174191
Mechanical data		
Weight	[g]	11.4
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	36.8 x 10.2 x 16
Materials		PBT
Tightening torque	[Nm]	< 0.5; (with washer)
Displays / operating elements		
Display	switching status	4 x 90° LED, yellow
Remarks		
Pack quantity		1 pcs.

IS5044



Inductive sensor

IS-2002-FRKG/AS

Electrical connection - plug

Connector: 1 x M8; coding: A

