




Capacitive sensor

KI-2200NFBOAP2T/LS100



- 1 LED ring
- 2 programming buttons



Product characteristics		
Output function		normally open / normally closed; (selectable)
Sensing range	[mm]	20
Housing		threaded type
Dimensions	[mm]	M30 x 1.5 / L = 90
Electrical data		
Operating voltage	[V]	30...250 AC / 20...250 DC
Rated insulation voltage	[V]	250
Protection class		II
Reverse polarity protection		yes
Max. power-on delay time	[ms]	700
Outputs		
Output function		normally open / normally closed; (selectable)
Max. voltage drop switching output DC	[V]	8
Max. voltage drop switching output AC	[V]	10
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5 (250 V AC) / 1.7 (110 V AC) / 1.5 (24 V DC)
Permanent current rating of switching output AC	[mA]	100; (150 (...40 °C))
Permanent current rating of switching output DC	[mA]	100; (150 (...40 °C))
Short-time current rating of switching output	[mA]	1000; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	10
Switching frequency DC	[Hz]	10
Short-circuit proof		no
Overload protection		no

KI0064



Capacitive sensor

KI-2200NFBOAP2T/LS100

Detection zone		
Sensing range	[mm]	20
Accuracy / deviations		
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-20...20
Software / programming		
Parameter setting options	7 output hold times programmable; (1: 0 s; 2: 2 s; 3: 4 s; 4: 6 s; 5: 8 s; 6: 10 s; 7: 12 s)	
Operating conditions		
Ambient temperature	[°C]	-25...80
Note on ambient temperature	temperature of the sensing face: -25...110 °C	
Protection	IP 65; IP 67	
Tests / approvals		
EMC	EN 61000-4-2	4 kV CD / 8 kV AD
	EN 61000-4-3	3 V/m
	EN 61000-4-4	2 kV
	EN 61000-4-6	3 V
	EN 55011	class B
Mechanical data		
Weight	[g]	88.3
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 90
Thread designation	M30 x 1.5	
Materials	housing: PBT; pushbuttons: TPE-U; LED window: PC	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	
Electrical connection		
Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting	
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Remarks	Note:	
	Check the safe functioning of the unit after a short circuit.	
Pack quantity	1 pcs.	

KI0064




Capacitive sensor

KI-2200NFBOAP2T/LS100

Electrical connection - plug

Connector: 1 x 1/2"; coding: C



Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting