


KT5350



Capacitive illuminated pushbutton

KTMBF-ERGBPKG/2M



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	Ø 32 / L = 31

Application

Operating principle	bistable
---------------------	----------

Electrical data

Operating voltage [V]	12...30 DC
Current consumption [mA]	30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	500

Outputs

Electrical design	PNP
Output function	normally open
Permanent current rating of switching output DC [mA]	200
Short-circuit protection	yes
Overload protection	yes

Response times

Response time [ms]	35
--------------------	----

Operating conditions

Ambient temperature [°C]	-40...85
Protection	IP 65; IP 67; IP 69K; (on the front)

Tests / approvals

EMC	IEC 61000-4
-----	-------------

Mechanical data

Weight [g]	119.5
------------	-------


KT5350



Capacitive illuminated pushbutton

KTMBF-ERGBPKG/2M

Dimensions	[mm]	Ø 32 / L = 31	
Materials	housing: stainless steel (1.4404 / 316L); active face: PA Grilamid TR 90UV		
Displays / operating elements			
Display	switching status	1 x LED, green	
	function	1 x LED, red can be triggered	
Аксессуары			
Items supplied	lock nuts: 1		
	Gasket: 1		
Accessories (optional)	symbol disc		
Remarks			
Pack quantity	1 pcs.		
Electrical connection			
Cable: 2 m, PUR			
Connection			



	Core colours :
BK =	black
BN =	brown
BU =	blue
YE =	yellow