



T-slot cylinder sensor with reed contact

MRT3021BBKOA/R/ZH



- 1 fastening clamp with combined slot / hexagon socket head
hexagonal socket AF 1.5
2 Sensing face



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	30.5 x 5 x 6.5

Electrical data

Operating voltage [V]	5...50 AC/DC; (External protective circuit for inductive load (valve, contactor, etc.) necessary. ; "supply class 2" to cULus)
Protection class	III
Reverse polarity protection	yes
Reverse polarity protection	no

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1
Max. voltage drop switching output AC [V]	1
Permanent current rating of switching output AC [mA]	350
Permanent current rating of switching output DC [mA]	500
Switching frequency AC [Hz]	1000
Switching frequency DC [Hz]	1000
Max. switching power [W]	10
Short-circuit protection	no
Short-circuit proof	no

MR0122



T-slot cylinder sensor with reed contact

MRT3021BBKOA/R/ZH

Overload protection	no	
Detection zone		
Response sensitivity	[mT]	2.1
Travel speed	[m/s]	10
Accuracy / deviations		
Hysteresis	[mm]	1
Repeatability	[mm]	< 0.2
Response times		
Max. fall time	[ms]	0.1
Max. make time incl. bounce	[ms]	0.6
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 65; IP 67	
Tests / approvals		
EMC	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[ANN]	20385
UL approval	UL Approval no.	C004
Mechanical data		
Weight	[g]	28.8
Mounting	flush mountable	
Cylinder type	T-slot cylinders	
Dimensions	[mm]	30.5 x 5 x 6.5
Materials	PA; fastening clamp: stainless steel	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Electrical connection		
Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 0,75 A; fast acting; DC operation; ≤ 0,6 A; fast acting; AC operation	
Аксессуары		
Items supplied	rubber placeholder: 1	
	Cable clip: 1	
Remarks		
Pack quantity	1 pcs.	

MR0122




T-slot cylinder sensor with reed contact

MRT3021BBKOA/R/ZH

Electrical connection

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



Note miniature fuse to IEC60127-2 sheet 1

≤ 0.75 A fast acting DC operation

≤ 0.6 A fast acting AC operation

Core colours :

BK = black
BN = brown
BU = blue