




Diffuse reflection sensor with background suppression

OIH-HPKG/US/600MM

Article no longer available - archive entry



1 potentiometer



Product characteristics

Type of light	red light
---------------	-----------

Application

Special feature	Background suppression
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	35
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	625


Outputs

Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	300
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes



Diffuse reflection sensor with background suppression

OIH-HPKG/US/600MM

Detection zone		
Range	[mm]	< 600; (white paper 200 x 200 mm 90% remission)
Range on white object (90 % remission)	[mm]	< 600
Range on grey object (18 % remission)	[mm]	< 596
Range on black object (6 % remission)	[mm]	< 578
Range adjustable		no
Max. light spot diameter	[mm]	30
Light spot dimensions refer to		at maximum range
Background suppression available		yes
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	211
Dimensions	[mm]	64 x 43 x 38
Thread designation		M30 x 1.5
Materials		diecast zinc nickel-plated
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Аксессуары		
Items supplied	lock nut: 1	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A		
		



Diffuse reflection sensor with background suppression

OIH-HPKG/US/600MM

Connection

