


Article no longer available - archive entry

**Product characteristics**

Process connection	G 1/2 external thread
--------------------	-----------------------

Application

Media	Liquids
Pressure rating [bar]	30

Electrical data

Operating voltage [V]	26.5...31.6 DC
Current consumption [mA]	< 45
Protection class	II
Reverse polarity protection	yes
Power-on delay time [s]	< 20

Outputs

Electrical design	AS-i
Overload protection	yes

Measuring/setting range

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

Response times

Response time [s]	1...10
-------------------	--------



Flow monitor

SCR12ABAASI /US-100

Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...80
Protection		IP 67
AS-i classification		
AS-i I/O configuration	[hex]	1
AS-i ID code	[hex]	1
Mechanical data		
Materials		PBT-GF20
Materials (wetted parts)		stainless steel (1.4305 / 303)
Process connection		G 1/2 external thread
Displays / operating elements		
Display	function	11 x LED
Аксессуары		
Items supplied		sealings: 2 x AMF 30 screwdrivers
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Connector: 1 x M12; coding: A



Connection

