




AS-Interface motor starter for three-phase motors

PowerSwitch 0,4A 0,09KW



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 250
Max. current load total	[A]	0.3
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4; Number of digital outputs: 4
------------------------------	---

Inputs

Number of digital inputs	4
Input circuit of digital inputs	PNP



AS-Interface motor starter for three-phase motors

PowerSwitch 0,4A 0,09KW

Sensor supply of the inputs		AS-i
Подача напруги [V]		20...30
Max. total current rating of inputs [mA]		140
Input current High [mA]		6...10
Input current Low [mA]		0...2
Switching level high [V]		> 10
Digital inputs protected against short circuits		yes
Outputs		
Electrical design		AS-i
Number of digital outputs		4
Voltage range DC [V]		18...30; (to PELV)
Voltage range AC [V]		110...400
Max. current load per output [mA]		150; (external outputs: Short-circuit proof; reversing contactor: not protected against short circuits)
Electrically separated		yes
Operating conditions		
Ambient temperature [°C]		0...60
Protection		IP 54
Tests / approvals		
EMC	EN 50081-1	
	EN 61000-6-2	
AS-i classification		
AS-i version		2.0
Розширений режим адресації		no
AS-i profile		S-7.0
AS-i I/O configuration [hex]		7
AS-i ID code [hex]		0
Mechanical data		
Weight [g]		1845
Type of mounting		backplane mounting
Dimensions [mm]		180 x 182 x 90
Materials		PC glass fibre reinforced; flame-retardant; UV resistant
Displays / operating elements		
Display	switching status	LED, yellow
	operation	LED, green
	errors	LED, red
Remarks		
Remarks	The PowerSwitch motor starter uses two outputs to trigger the reversing contactors (motor right/left/off).	
	Two further outputs can be connected at will.	
	The messages "motor protection activated" and "hand-held operating panel connected" are indicated via the input data bits.	
	Sensors can be connected to two additional inputs.	



AS-Interface motor starter for three-phase motors

PowerSwitch 0,4A 0,09KW

Pack quantity

1 pcs.

Electrical connection

	400 V connection and motor socket
L1	contact number 1
L2	contact number 2
L3	contact number 3
PE	prepared for PE
	supply voltage connector
1	AS-i +
2	24V DC -
3	AS-i -
4	24V DC +
	output socket 2 x M12
1	I+
2/4	input bridged
3	I-
	output socket 2 x M12
1	n.c.
2	n.c.
3	24V DC -
4	switching output 24V DC +