


DF2210



Electronic circuit breaker

Fuse/IO-Link/24VDC/10A



- 1 panel for labelling
- 2 pushbutton on / off / reset Status LED 1
- 3 push-in terminal Output 1



Electrical data		
Operating voltage	[V]	to SELV/PELV
Nominal voltage DC	[V]	24
Input voltage DC	[V]	18...30
Protection class		III
Mains buffering time (nominal voltage 24 V DC)	[ms]	10
Closed-circuit current	[mA]	10
Number of channels		1
Nominal current	[A]	10
Nominal current (Fail Safe Element)	[A]	10
Outputs		
Load capacitance, total	[mF]	20
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...70
Protection		IP 20; (on the front)
Degree of soiling		2
Tests / approvals		
EMC	EN 61000-6-3	radiation of interference
	EN 61000-6-2	noise immunity
Mechanical data		
Weight	[g]	72
Dimensions	[mm]	80 x 12.5 x 98.5

DF2210



Electronic circuit breaker

Fuse/IO-Link/24VDC/10A


Displays / operating elements

Display	status	1 x LED, red / green / orange
Operating elements	1 x	pushbuttons

Electrical connection


push-in terminals:
contact lever/strip:

Connection



Diagrams and graphs

Output curve



Time-current characteristics