



Switching amplifier

N600/230VAC/0,1A

Article no longer available - archive entry

Alternative articles: DN0210

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available



Product characteristics

Housing	housing for DIN rail mounting
---------	-------------------------------

Application

Application	Power supply and signal evaluation
-------------	------------------------------------

Electrical data

Nominal voltage AC	[V]	< 230
Nominal voltage tolerance	[%]	10
Nominal voltage tolerance 2	[%]	10
Nominal frequency AC	[Hz]	47...63
Auxiliary energy for sensors DC	[V]	24; ($\pm 5\%$, $\leq 100\text{ mA}$)

Inputs / outputs

Number of inputs and outputs	Number of relay outputs: 1
------------------------------	----------------------------

Outputs

Number of relay outputs	1
Contact rating	8 A / 1250 VA / 250 V AC

Operating conditions

Ambient temperature	[°C]	0...50
Protection		IP 40
Protection rating terminals		IP 20

DN0001



Switching amplifier

N600/230VAC/0,1A

Mechanical data		
Weight	[g]	0.43
Housing	housing for DIN rail mounting	
Material	plastics	
Displays / operating elements		
Display	Switching status	LED, red
	Power	1 x LED, green
Electrical connection		
terminals: ...4 mm²		
Connection		

