

E10419



Female cordset

ADOGH040SCS0005F03

Article no longer available - archive entry



Electrical data

Operating voltage [V] < 250 AC / < 300 DC

Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

Mechanical data

Dimensions [mm] 15 x 15 x 43

Material TPU (urethane)

Molded-body material TPU (urethane)

Material nut brass, weld coated

Remarks


Pack quantity 1 pcs.

Electrical connection

Cable: 5 m, PVC, orange, Ø 5 mm; cross-linked; 3 x 0.34 mm² (19 x Ø 0.15 mm)

Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, weld coated; Tightening torque: 0.5 Nm



E10419



Female cordset

ADOGH040SCS0005F03

Connection



BN =
BK =
BU =

Core colors :
brown
black
blue