


E10432



Female cordset

ADOGH040MSS0005G04

Article no longer available - archive entry



Application

System	screened cable
--------	----------------

Electrical data

Operating voltage	[V]	< 50 AC / < 60 DC
Protection class		III

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Mechanical data

Dimensions	[mm]	15 x 15 x 43
Material		TPU (urethane)
Molded-body material		TPU (urethane)
Material nut		brass, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

E10432



Female cordset

ADOGH040MSS0005G04

Electrical connection


Cable: 5 m, PVC, orange, Ø 5 mm, screened; 4 x 0.25 mm² (32 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated; Tightening torque: 0.5 Nm;
Shielded connection cable: shield not connected



Connection



	Core colors :
BN =	brown
BK =	black
BU =	blue
WH =	white