

E10516



Female cordset

ADOAH042MSS0005E03

Article no longer available - archive entry



Electrical data

Operating voltage [M] 10...30 DC

Outputs

Electrical design PNP

Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

Mechanical data

Material TPU (urethane) transparent

Molded-body material TPU (urethane), transparent

Material nut brass, nickel-plated

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Remarks

Pack quantity 1 pcs.

E10516



Female cordset

ADOAH042MSS0005E03

Electrical connection

Cable: 5 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm²

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane), transparent; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm



Connection



BN =	Core colors :
BK =	brown
BU =	black
	blue