

E10630




Female cordset

ADOGF030ZDS0005A03

Article no longer available - archive entry

Alternative articles: E11487
When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	< 60 AC/DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 68
Mechanical data		
Dimensions	[mm]	10 x 10 x 33
Material		PUR
Molded-body material		PUR
Material nut		diecast zinc
Remarks		
Pack quantity		1 pcs.

E10630



Female cordset

ADOGF030ZDS0005A03

Electrical connection


Cable: 5 m, PUR / PVC, black, Ø 4.5 mm; 3 x 0.25 mm² (128 x Ø 0.05 mm)

Electrical connection - Socket

Connector: 1 x M8, straight; coding: A; Moulded body: PUR; Locking: diecast zinc



Connection



BK =	Core colors :
BN =	black
BU =	brown
	blue