

E10679



Female cordset

ADOAH042MSS0006B04

Article no longer available - archive entry



Electrical data

Operating voltage [V] 10...30 DC

Outputs

Electrical design PNP

Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

Mechanical data

Dimensions [mm] 27 x 15 x 39

Material TPU (urethane) transparent

Molded-body material TPU (urethane), transparent

Material nut brass, nickel-plated

Displays / operating elements

Display Switching status 1 x LED, yellow

Power 1 x LED, green

Remarks

Pack quantity 1 pcs.

E10679



Female cordset

ADOAH042MSS0006B04

Electrical connection


Cable: 6 m, PUR, orange, Ø 5 mm; 4 x 0.25 mm² (128 x Ø 0.05 mm)

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane), transparent; Locking: brass, nickel-plated



Connection



BK =	Core colors :
BN =	black
BU =	brown
WH =	blue
	white