


E10714



Female cordset

ADOAF030ZDS0010A03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 60 AC/DC
Protection class		III


Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 68

Mechanical data		
Dimensions	[mm]	17 x 10 x 27
Material		PUR
Molded-body material		PUR
Material nut		diecast zinc

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 10 m, PUR / PVC, black, Ø 4.5 mm; 3 x 0.25 mm² (128 x Ø 0.05 mm)		

Electrical connection - Socket		
Connector: 1 x M8, angled; coding: A; Moulded body: PUR; Locking: diecast zinc		




E10714



Female cordset

ADOAF030ZDS0010A03

Connection



BN =	Core colors :	brown
BK =		black
BU =		blue