

E10792



Female cordset

ADOAH040MSS0010A03

Article no longer available - archive entry

Alternative articles: EVC006
When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	27 x 15 x 39
Material		TPU (urethane)
Molded-body material		TPU (urethane)
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E10792



Female cordset

ADOAH040MSS0010A03

Electrical connection

Cable: 10 m, PUR / PVC, black; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated



Connection



BN =	Core colors :
BK =	brown
BU =	black
	blue