

E10909



Female cordset

ADOAH040SCS0002I04

Article no longer available - archive entry

Alternative articles: EVW004
When selecting an alternative article and accessories please note that technical data may differ!



Application		
System		Free from silicone; Halogen-free; gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 68
Mechanical data		
Dimensions	[mm]	27 x 15 x 39
Material		TPU (urethane)
Molded-body material		TPU (urethane)
Material nut		brass, weld coated
Remarks		
Pack quantity		1 pcs.

E10909



Female cordset

ADOAH040SCS0002I04

Electrical connection

Cable: 2 m, PUR, Halogen-free, black, Ø 4.8 mm; cross-linked; 4 x 0.34 mm² (19 x Ø 0.15 mm)

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane); Locking: brass, weld coated; Contacts: gold-plated; Tightening torque: 0.5 Nm



Connection



Core colors :
BK = black
BN = brown
BU = blue
WH = white