

E10928



Connection cable

VDOGF030MSS00,6H03STGF030MSS

Article no longer available - archive entry



Application	
System	Halogen-free
Electrical data	
Operating voltage [V]	10...55 DC
Protection class	III
Operating conditions	
Ambient temperature [°C]	-25...90
Protection	IP 67
Mechanical data	
Material	TPU (urethane)
Molded-body material	TPU (urethane)
Material nut	brass, nickel-plated
Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated



E10928



Connection cable

VDOGF030MSS00,6H03STGF030MSS

Electrical connection

Cable: 0.6 m, Halogen-free; 3 x 0.34 mm²

Connection



Electrical connection - Socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated

