




Patchcords with valve plug

AVDAB031--S0002A03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 24 AC/DC
Overvoltage protection		yes; (VDR)

Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67

Mechanical data		
Dimensions	[mm]	26.5 x 22.4 x 43.5
Material		PVC
Molded-body material		PVC
Material nut		stainless steel (1.4404 / 316L)

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 2 m, PUR / PVC; 3 x 0.5 mm²		

Electrical connection - Socket		
Connector: 1 x valve type B DIN, angled; Moulded body: PVC; Locking: stainless steel (1.4404 / 316L)		




E10972



Patchcords with valve plug

AVDAB031--S0002A03

Connection



BN =	Core colors :
BU =	brown
GN/YE =	blue
	green/yellow