

E10097




Female cordset

ADOAH040PLS0002E03

Article no longer available - archive entry

Alternative articles: E10909
When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	10...55 DC
Operating conditions		
Ambient temperature	[°C]	-40...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	25 x 15 x 32
Material		PUR
Molded-body material		PUR
Material nut		PUR
Remarks		
Pack quantity		1 pcs.

E10097



Female cordset

ADOAH040PLS0002E03

Electrical connection

Cable: 2 m, PVC; 3 x 0.34 mm² (7 x Ø 0.25 mm)

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: PUR



Connection

