


E10128



Female cordset

ADOAH040PLS0005E03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...55 DC
Operating conditions		
Ambient temperature	[°C]	-40...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	25 x 15 x 32
Material		PUR
Molded-body material		PUR
Material nut		PUR
Remarks		
Pack quantity		1 pcs.

Electrical connection	
Cable: 5 m, PVC; 3 x 0.34 mm ² (7 x Ø 0.25 mm)	

Electrical connection - Socket	
Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: PUR	



E10128



Female cordset

ADOAH040PLS0005E03

Connection

