


E10171



Female cordset

ADOGH040MSS0005B03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	15 x 15 x 43
Material		TPU (urethane)
Molded-body material		TPU (urethane)
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 5 m, PUR, orange, Ø 5 mm; 3 x 0.34 mm ² (42 x Ø 0.1 mm)		
Electrical connection - Socket		

Connector: 1 x M12, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated




E10171



Female cordset

ADOGH040MSS0005B03

Connection



BN =	Core colors :
BK =	brown
BU =	black
	blue