

E11050



Patchcords with valve plug

AVDAA031--S0002A03

Article no longer available - archive entry



Electrical data

Operating voltage	[V]	< 24 AC/DC
Overvoltage protection		yes; (VDR)

Operating conditions

Ambient temperature	[°C]	-25...90
Protection		IP 67

Mechanical data

Material	PUR
Molded-body material	PUR

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	screw
	panel for labelling

Remarks

Pack quantity	1 pcs.
---------------	--------

E11050



Patchcords with valve plug

AVDAA031--S0002A03

Electrical connection

Cable: 2 m, PUR / PVC; 3 x 0.5 mm² (16 x Ø 0.2 mm)

Electrical connection - Socket

Connector: 1 x valve type A DIN, angled; Moulded body: PUR



Connection



BN = Core colors :
brown
BU = blue
GN/YE = green/yellow