

# E11157



## Patchcords with valve plug

VVDAB031--S01,5H03STGH030MSS

Article no longer available - archive entry



### Application

System Halogen-free

### Electrical data

Operating voltage [V] < 24 AC/DC

Overvoltage protection yes; (VDR)

### Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

### Mechanical data

Dimensions [mm] 15 x 15 x 46.5

Material TPU (urethane)

Molded-body material TPU (urethane)

Material nut brass, nickel-plated

### Displays / operating elements

Display Switching status 1 x LED, yellow

### Accessories

Items supplied screw  
panel for labelling

### Remarks

Pack quantity 1 pcs.

# E11157



## Patchcords with valve plug

VVDAB031--S01,5H03STGH030MSS

### Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU (urethane); Locking: brass, nickel-plated



### Electrical connection

Cable: 1.5 m, PUR, Halogen-free; 3 x 0.5 mm<sup>2</sup>

### Connection



### Electrical connection - Socket

Connector: 1 x valve type B DIN, angled; Moulded body: TPU (urethane); Locking: brass, nickel-plated

