


E11301



Connection cable

VDOAH040MSS0005H04STGH040MSS

Article no longer available - archive entry



Application	
System	Halogen-free
Electrical data	
Operating voltage	[V] < 250 AC / < 300 DC
Operating conditions	
Ambient temperature	[°C] -25...80
Protection	IP 68
Mechanical data	
Material	PUR
Molded-body material	PUR
Material nut	brass, nickel-plated
Remarks	
Pack quantity	1 pcs.
Electrical connection - plug	

Connector: 1 x M12, straight; coding: A; Moulded body: PUR; Locking: brass, nickel-plated



E11301




Connection cable

VDOAH040MSS0005H04STGH040MSS

Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: brass, nickel-plated

