


E12614



Female cordset

Fuse/IO-Link/Cable/2m



Application		
System		Halogen-free
Electrical data		
Operating voltage	[V]	< 50 AC/DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Mechanical data		
Weight	[g]	62.1
Material		brass nickel-plated; housing: TPU (urethane)
Remarks		
Pack quantity		1 pcs.

E12614



Female cordset

Fuse/IO-Link/Cable/2m

Electrical connection

Cable: 2 m, PUR, Halogen-free, black, Ø 4.9 mm; 3 x 0.34 mm²

Electrical connection

Connection

