




Fiber optic diffuse reflection sensor

FT-00-M-V-E1



Application		
Function principle	Diffuse reflection sensor	
Application	High temperature resistance; Robust design for use in harsh industrial environments; Resistant to various aggressive chemicals	
Monitoring range		
Range with fiber optic amplifier type	OKF; OUF; OOF	
OKF		
Range fiber optics	[mm]	8
OOF		
Range fiber optics	[mm]	24
OUF		
Range fiber optics	[mm]	8
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Weight	[g]	51
Version of sensing head	straight	
Sensing head diameter	[mm]	1
Sensing head length	[mm]	5
Total length	[mm]	600

E20507



Fiber optic diffuse reflection sensor

FT-00-M-V-E1

Min. bending radius	[mm]	20
Fiber arrangement		
Fiber material		glass
Fiber head material		stainless steel (1.4305 / 303)
Fiber sheath material		metal silicone
Accessories		
Items supplied		E20103
Remarks		
Pack quantity		1 pcs.