




Fiber optic through beam sensor

FE-00-M-V-M4/1m

Article no longer available - archive entry

Alternative articles: E20533
When selecting an alternative article and accessories please note that technical data may differ!



Application	
Function principle	Through-beam sensor
Monitoring range	
Range with fiber optic amplifier type	OKF; OUF
OKF	
Range of fiber optics [mm]	120
OUF	
Range of fiber optics [mm]	120
Operating conditions	
Ambient temperature [°C]	-20...150
Mechanical data	
Version of sensing head	straight
Sensing head thread	M4
Sensing head length [mm]	15
Total length [mm]	1000

E20532



Fiber optic through beam sensor

FE-00-M-V-M4/1m

Min. bending radius	[mm]	20
Fiber material		glass
Fiber head material		stainless steel (1.4305 / 303)
Fiber sheath material		metal silicone
Remarks		
Pack quantity		1 pcs.