




Fiber optic through beam sensor

FE-00-M-V-R3/2,5m

Article no longer available - archive entry



Application		
Function principle		Through-beam sensor
Monitoring range		
Range with fiber optic amplifier type		OKF; OUF
OKF		
Range of fiber optics	[mm]	85
OUF		
Range of fiber optics	[mm]	85
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Version of sensing head		angled
Sensing head diameter	[mm]	3
Sensing head length	[mm]	10
Total length	[mm]	2500
Min. bending radius	[mm]	20
Fiber material		glass
Fiber head material		stainless steel (1.4305 / 303)

E20542



Fiber optic through beam sensor

FE-00-M-V-R3/2,5m

Fiber sheath material	metal silicone
Remarks	
Pack quantity	1 pcs.