



Fiber optic through beam sensor

FE-50-V-V-E2,3

Article no longer available - archive entry

No scale drawing available

Application

Function principle	Through-beam sensor
--------------------	---------------------

Monitoring range

Range with fiber optic amplifier type	OBF
---------------------------------------	-----

OBF

Range of fiber optics [mm]	110
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-58...315
--------------------------	-----------

Mechanical data

Version of sensing head	straight
Sensing head diameter [mm]	8
Total length [mm]	900
Min. bending radius [mm]	19
Fiber material	glass
Fiber head material	stainless steel (1.4305 / 303)
Fiber sheath material	stainless steel (1.4305 / 303)

Remarks

Pack quantity	1 pcs.
---------------	--------