




Fiber optic through beam sensor

FE-00-P-A-R3/2,5M

Article no longer available - archive entry



Application

Function principle

Through-beam sensor

Monitoring range

Range with fiber optic
amplifier type

OKF; OUF

OKF

Range of fiber optics

[mm]

90

OUF

Range of fiber optics

[mm]

90

Operating conditions

Ambient temperature

[°C]

-20...80

Mechanical data

Version of sensing head

angled

Sensing head diameter

[mm]

3

Sensing head length

[mm]

10

Total length

[mm]

2500

Min. bending radius

[mm]

10

Material

Adapter: PPE

Fiber material

glass

E20140



Fiber optic through beam sensor

FE-00-P-A-R3/2,5M

Fiber head material	aluminum
Fiber sheath material	PVC
Remarks	
Pack quantity	1 pcs.