



Fiber optic diffuse reflection sensor

FT-00-M-V-M6/0,3M

Article no longer available - archive entry

Alternative articles: E20489

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Monitoring range

Range with fiber optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range fiber optics	[mm]	20
--------------------	------	----

OUF

Range fiber optics	[mm]	20
--------------------	------	----

Operating conditions

Ambient temperature	[°C]	-20...80
---------------------	------	----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M6
Total length	[mm] 300
Min. bending radius	[mm] 20
Fiber material	acrylic
Fiber head material	stainless steel (1.4305 / 303)
Fiber sheath material	metal silicone

Remarks

Pack quantity	1 pcs.
---------------	--------