

Fiber optic through beam sensor

FE-30-P-A-E3/3M

Article no longer available - archive entry



Application

Function principle

Through-beam sensor

Monitoring range

Range with fiber optic
amplifier type

OIF

OIF

Range of fiber optics

[mm]

64

Operating conditions

Ambient temperature

[°C]

-20...80

Mechanical data

Version of sensing head

straight

Sensing head diameter

[mm]

3

Total length

[mm]

3000

Min. bending radius

[mm]

30

Material

Adapter: PA

Fiber material

glass

Fiber head material

aluminum

Fiber sheath material

PVC

E20337



Fiber optic through beam sensor

FE-30-P-A-E3/3M

Remarks	
---------	--

Pack quantity	1 pcs.
---------------	--------