

E20346




Fiber optic through beam sensor

FE-30-A-A-E3/2m

Article no longer available - archive entry

Alternative articles: E20347
When selecting an alternative article and accessories please note that technical data may differ!



Application	
Function principle	Through-beam sensor
Monitoring range	
Range with fiber optic amplifier type	OIF
OIF	
Range of fiber optics [mm]	80
Operating conditions	
Ambient temperature [°C]	-40...290
Mechanical data	
Version of sensing head	straight
Sensing head diameter [mm]	3
Total length [mm]	2000
Min. bending radius [mm]	30
Material	Adapter: PA
Fiber material	glass
Fiber head material	aluminum

E20346



Fiber optic through beam sensor

FE-30-A-A-E3/2m

Fiber sheath material	aluminum
Remarks	
Pack quantity	1 pcs.