



Fiber optic through beam sensor

FE-00-A-V-E1/2,5m

Article no longer available - archive entry



Application

Function principle

Through-beam sensor

Monitoring range

Range with fiber optic
amplifier type

OKF; OUF

OKF

Range of fiber optics

[mm]

36

OUF

Range of fiber optics

[mm]

36

Operating conditions

Ambient temperature

[°C]

-40...290

Mechanical data

Version of sensing head

straight

Sensing head diameter

[mm]

1

Sensing head length

[mm]

5

Total length

[mm]

2500

Min. bending radius

[mm]

20

Material

Adapter: ABS

Fiber material

glass

E20372



Fiber optic through beam sensor

FE-00-A-V-E1/2,5m

Fiber head material	stainless steel (1.4305 / 303)
Fiber sheath material	aluminum
Remarks	
Pack quantity	1 pcs.