





Fiber optic through beam sensor

FE-18-P-A-M4

Article to be discontinued



Application		
Function principle	Through-beam sensor	
Application	For use in industrial environments	
Monitoring range		
Range with fiber optic amplifier type	OGF	
OGF		
Range of fiber optics	[mm]	80
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Weight	[g]	50
Version of sensing head	straight	
Sensing head thread	M4	
Sensing head length	[mm]	15
Total length	[mm]	600
Min. bending radius	[mm]	20
Fiber arrangement		
Material	Adapter: PPE	

E20387



Fiber optic through beam sensor

FE-18-P-A-M4

Fiber material	glass
Fiber head material	aluminum
Fiber sheath material	PVC
Accessories	
Items supplied	Hexagon nuts: 4 x M4
	tooth lock washers: 4
Remarks	
Pack quantity	1 pcs.