




Mounting adapter for process sensors

ADAPT IFM-SUEDMO DN25 O-RG

Article no longer available - archive entry



- 1 Aseptoflex thread
2 Aseptoflex sealing edge

Application

Installation	with O-ring
Pressure rating [bar]	16

Tests / approvals

Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.

Mechanical data

Type of mounting	with O-ring
Material	stainless steel (1.4404 / 316L)
Sensor connection	Aseptoflex
Process connection	Clamp DN25
Surface characteristics Ra/Rz of the wetted parts	0.4 / 4
Hygienic equipment class to DIN 11866	H4

Remarks

Pack quantity	1 pcs.
---------------	--------