




Mounting adapter for process sensors

ADAPT IFM-SMS DN50(2)GWD

Article no longer available - archive entry



- 1 Aseptoflex thread
- 2 Aseptoflex sealing edge

Application

Pressure rating [bar] 25

Tests / approvals

Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.

Mechanical data

Material	stainless steel (1.4404 / 316L)
Sensor connection	Aseptoflex
Process connection	flange DN50 (2")
Surface characteristics Ra/Rz of the wetted parts	0.4 / 4
Hygienic equipment class to DIN 11866	H4

Remarks

Pack quantity	1 pcs.
---------------	--------