


E37230



Thermowell for temperature sensors

THERMOWELL, D6/1/2"NPT/L=230



Application		
Design		for temperature sensors EL = 300 mm
Pressure rating	[bar]	400
Accuracy / deviations		
Max. permissible flow velocity	[m/s]	12
Mechanical data		
Weight	[g]	354.6
Material		stainless steel (1.4404 / 316L)
Sensor connection		1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT
Process connection		1/2" NPT
Installation length EL	[mm]	201
Bore length BL	[mm]	228.6
Remarks		
Pack quantity		1 pcs.